



WELDED LINK CHAIN ON REELS -DIN5685 SPECIFICATION

CPL Product Code	Material Dia	Inside Length	Inside Width	Surface Finish	Reel Length	Max. Rec. Load
SW-A20BLK	2.0mm	12.0mm	5.0mm	Black Plated	50 mtrs	20 kgs
SW-A20BZP	2.0mm	12.0mm	5.0mm	Bright Zinc Plated	50 mtrs	20 kgs
SW-A20HDG	2.0mm	12.0mm	5.0mm	Hot Dip Galvanised	50 mtrs	20 kgs
SW-C20BLK	2.0mm	22.0mm	4.0mm	Black Plated	50 mtrs	20 kgs
SW-C20BZP	2.0mm	22.0mm	4.0mm	Bright Zinc Plated	50 mtrs	20 kgs
SW-C20HDG	2.0mm	22.0mm	4.0mm	Hot Dip Galvanised	50 mtrs	30 kgs
SW-A25BLK	2.5mm	14.0mm	5.0mm	Black Plated	30 mtrs	30 kgs
SW-A25BRS	2.5mm	14.0mm	5.0mm	Brass Plated	30 mtrs	30 kgs
SW-A25BZP	2.5mm	14.0mm	5.0mm	Bright Zinc Plated	30 mtrs	30 kgs
SW-A25HDG	2.5mm	14.0mm	5.0mm	Hot Dip Galvanised	30 mtrs	30 kgs
SW-C25BLK	2.5mm	24.0mm	5.0mm	Black Plated	30 mtrs	30 kgs
SW-C25BZP	2.5mm	24.0mm	5.0mm	Bright Zinc Plated	30 mtrs	30 kgs
SW-C25HDG	2.5mm	24.0mm	5.0mm	Hot Dip Galvanised	30 mtrs	30 kgs
SW-A30BLK	3.0mm	16.0mm	8.0mm	Black Plated	30 mtrs	40 kgs
SW-A30BZP	3.0mm	16.0mm	8.0mm	Bright Zinc Plated	30 mtrs	40 kgs
SW-A30HDG	3.0mm	16.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
SW-B30BLK	3.0mm	21.0mm	8.0mm	Black Plated	30 mtrs	40 kgs
SW-B30BRS	3.0mm	21.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
SW-B30BZP	3.0mm	21.0mm	8.0mm	Bright Zinc Plated	30 mtrs	40 kgs
SW-B30HDG	3.0mm	21.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
SW-C30BLK	3.0mm	26.0mm	8.0mm	Black Plated	30 mtrs	40 kgs
SW-C30BZP	3.0mm	26.0mm	8.0mm	Bright Zinc Plated	30 mtrs	40 kgs
SW-C30HDG	3.0mm	26.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
SW-A40BLK	4.0mm	19.0mm	9.0mm	Black Plated	30 mtrs	80 kgs
SW-A40BZP	4.0mm	19.0mm	9.0mm	Bright Zinc Plated	30 mtrs	80 kgs
SW-A40HDG	4.0mm	19.0mm	9.0mm	Hot Dip Galvanised	30 mtrs	80 kgs
SW-C40BLK	4.0mm	32.0mm	9.0mm	Black Plated	30 mtrs	80 kgs
SW-C40BZP	4.0mm	32.0mm	9.0mm	Bright Zinc Plated	30 mtrs	80 kgs
SW-C40HDG	4.0mm	32.0mm	9.0mm	Hot Dip Galvanised	30 mtrs	80 kgs
SW-A50BLK	5.0mm	21.0mm	11.0mm	Black Plated	30 mtrs	125 kgs
SW-A50BZP	5.0mm	21.0mm	11.0mm	Bright Zinc Plated	30 mtrs	125 kgs
SW-A50HDG	5.0mm	21.0mm	11.0mm	Hot Dip Galvanised	30 mtrs	125 kgs
SW-C50BLK	5.0mm	35.0mm	11.0mm	Black Plated	30 mtrs	125 kgs
SW-C50BZP	5.0mm	35.0mm	11.0mm	Bright Zinc Plated	30 mtrs	125 kgs
SW-50HDG	5.0mm	35.0mm	11.0mm	Hot Dip Galvanised	30 mtrs	125 kgs

Continued.....



WELDED LINK CHAIN ON REELS -DIN5685 SPECIFICATION

CPL Product Code	Material Dia	Inside Length	Inside Width	Surface Finish	Reel Length	Max. Rec. Load
SW-A60BLK	6.0mm	24.0mm	13.0mm	Black Plated	20 mtrs	160 kgs
SW-A60BZP	6.0mm	24.0mm	13.0mm	Bright Zinc Plated	20 mtrs	160 kgs
SW-A60HDG	6.0mm	24.0mm	13.0mm	Hot Dip Galvanised	20 mtrs	160 kgs
SW-B60BLK	6.0mm	33.0mm	13.0mm	Black Plated	20 mtrs	160 kgs
SW-B60BZP	6.0mm	33.0mm	13.0mm	Bright Zinc Plated	20 mtrs	160 kgs
SW-B60HDG	6.0mm	33.0mm	13.0mm	Hot Dip Galvanised	20 mtrs	160 kgs
SW-C60BLK	6.0mm	42.0mm	13.0mm	Black Plated	20 mtrs	160 kgs
SW-C60BZP	6.0mm	42.0mm	13.0mm	Bright Zinc Plated	20 mtrs	160 kgs
SW-C60HDG	6.0mm	42.0mm	13.0mm	Hot Dip Galvanised	20 mtrs	160 kgs
SW-A70BLK	7.0mm	28.0mm	14.0mm	Black Plated	15 mtrs	220 kgs
SW-A70BZP	7.0mm	28.0mm	14.0mm	Bright Zinc Plated	15 mtrs	220 kgs
SW-A70HDG	7.0mm	28.0mm	14.0mm	Hot Dip Galvanised	15 mtrs	220 kgs
SW-C70BLK	7.0mm	49.0mm	14.0mm	Black Plated	15 mtrs	220 kgs
SW-C70BZP	7.0mm	49.0mm	14.0mm	Bright Zinc Plated	15 mtrs	220 kgs
SW-C70HDG	7.0mm	49.0mm	14.0mm	Hot Dip Galvanised	15 mtrs	220 kgs
SW-A80BLK	8.0mm	32.0mm	16.0mm	Black Plated	15 mtrs	320 kgs
SW-A80BZP	8.0mm	32.0mm	16.0mm	Bright Zinc Plated	15 mtrs	320 kgs
SW-A80HDG	8.0mm	32.0mm	16.0mm	Hot Dip Galvanised	15 mtrs	320 kgs
SW-C80BLK	8.0mm	52.0mm	16.0mm	Black Plated	15 mtrs	320 kgs
SW-C80BZP	8.0mm	52.0mm	16.0mm	Bright Zinc Plated	15 mtrs	320 kgs
SW-C80HDG	8.0mm	52.0mm	16.0mm	Hot Dip Galvanised	15 mtrs	320 kgs
SW-A100BLK	10.0mm	40.0mm	20.0mm	Black Plated	15 mtrs	350 kgs
SW-A100BZP	10.0mm	40.0mm	20.0mm	Bright Zinc Plated	15 mtrs	350 kgs
SW-A100HDG	10.0mm	40.0mm	20.0mm	Hot Dip Galvanised	15 mtrs	350 kgs
SW-C100BLK	10.0mm	65.0mm	20.0mm	Black Plated	15 mtrs	350 kgs
SW-C100BZP	10.0mm	65.0mm	20.0mm	Bright Zinc Plated	15 mtrs	350 kgs
SW-C100HDG	10.0mm	65.0mm	20.0mm	Hot Dip Galvanised	15 mtrs	350 kgs

Please call if you require longer lengths, or if you have a project where you require chains to be supplied to a specified length.

Continued.....



WELDED LINK CHAIN IN BOXES -DIN5685 SPECIFICATION

CPL Product Code	Material Dia	Inside Length	Inside Width	Surface Finish	Boxed Length	Max. Rec. Load
BA20BLK	2.0mm	12.0mm	5.0mm	Black Plated	10 mtrs	20 kgs
BA20BZP	2.0mm	12.0mm	5.0mm	Bright Zinc Plated	10 mtrs	20 kgs
BA20HDG	2.0mm	12.0mm	5.0mm	Hot Dip Galvanised	10 mtrs	20 kgs
BC20BLK	2.0mm	22.0mm	4.0mm	Black Plated	10 mtrs	20 kgs
BC20BZP	2.0mm	22.0mm	4.0mm	Bright Zinc Plated	10 mtrs	20 kgs
BC20HDG	2.0mm	22.0mm	4.0mm	Hot Dip Galvanised	10 mtrs	30 kgs
BA25BLK	2.5mm	14.0mm	5.0mm	Black Plated	10 mtrs	30 kgs
BA25BRS	2.5mm	14.0mm	5.0mm	Brass Plated	10 mtrs	30 kgs
BA25BZP	2.5mm	14.0mm	5.0mm	Bright Zinc Plated	10 mtrs	30 kgs
BA25HDG	2.5mm	14.0mm	5.0mm	Hot Dip Galvanised	10 mtrs	30 kgs
BC25BLK	2.5mm	24.0mm	5.0mm	Black Plated	10 mtrs	30 kgs
BC25BZP	2.5mm	24.0mm	5.0mm	Bright Zinc Plated	10 mtrs	30 kgs
BC25HDG	2.5mm	24.0mm	5.0mm	Hot Dip Galvanised	10 mtrs	30 kgs
BA30BLK	3.0mm	16.0mm	8.0mm	Black Plated	10 mtrs	40 kgs
BA30BZP	3.0mm	16.0mm	8.0mm	Bright Zinc Plated	10 mtrs	40 kgs
BA30HDG	3.0mm	16.0mm	8.0mm	Hot Dip Galvanised	10 mtrs	40 kgs
BB30BLK	3.0mm	21.0mm	8.0mm	Black Plated	10 mtrs	40 kgs
BB30BRS	3.0mm	21.0mm	8.0mm	Hot Dip Galvanised	10 mtrs	40 kgs
BB30BZP	3.0mm	21.0mm	8.0mm	Bright Zinc Plated	10 mtrs	40 kgs
BB30HDG	3.0mm	21.0mm	8.0mm	Hot Dip Galvanised	10 mtrs	40 kgs
BC30BLK	3.0mm	26.0mm	8.0mm	Black Plated	10 mtrs	40 kgs
BC30BZP	3.0mm	26.0mm	8.0mm	Bright Zinc Plated	10 mtrs	40 kgs
BC30HDG	3.0mm	26.0mm	8.0mm	Hot Dip Galvanised	10 mtrs	40 kgs
BA40BLK	4.0mm	19.0mm	9.0mm	Black Plated	10 mtrs	80 kgs
BA40BZP	4.0mm	19.0mm	9.0mm	Bright Zinc Plated	10 mtrs	80 kgs
BA40HDG	4.0mm	19.0mm	9.0mm	Hot Dip Galvanised	10 mtrs	80 kgs
BC40BLK	4.0mm	32.0mm	9.0mm	Black Plated	10 mtrs	80 kgs
BC40BZP	4.0mm	32.0mm	9.0mm	Bright Zinc Plated	10 mtrs	80 kgs
BC40HDG	4.0mm	32.0mm	9.0mm	Hot Dip Galvanised	10 mtrs	80 kgs
BA50BLK	5.0mm	21.0mm	11.0mm	Black Plated	10 mtrs	125 kgs
BA50BZP	5.0mm	21.0mm	11.0mm	Bright Zinc Plated	10 mtrs	125 kgs
BA50HDG	5.0mm	21.0mm	11.0mm	Hot Dip Galvanised	10 mtrs	125 kgs
BC50BLK	5.0mm	35.0mm	11.0mm	Black Plated	10 mtrs	125 kgs
BC50BZP	5.0mm	35.0mm	11.0mm	Bright Zinc Plated	10 mtrs	125 kgs
B50HDG	5.0mm	35.0mm	11.0mm	Hot Dip Galvanised	10 mtrs	125 kgs

Continued.....



WELDED LINK CHAIN IN BOXES -DIN5685 SPECIFICATION


CPL Product Code	Material Dia	Inside Length	Inside Width	Surface Finish	Boxed Length	Max. Rec. Load
BA60BLK	6.0mm	24.0mm	13.0mm	Black Plated	10 mtrs	160 kgs
BA60BZP	6.0mm	24.0mm	13.0mm	Bright Zinc Plated	10 mtrs	160 kgs
BA60HDG	6.0mm	24.0mm	13.0mm	Hot Dip Galvanised	10 mtrs	160 kgs
BB60BLK	6.0mm	33.0mm	13.0mm	Black Plated	10 mtrs	160 kgs
BB60BZP	6.0mm	33.0mm	13.0mm	Bright Zinc Plated	10 mtrs	160 kgs
BB60HDG	6.0mm	33.0mm	13.0mm	Hot Dip Galvanised	10 mtrs	160 kgs
BC60BLK	6.0mm	42.0mm	13.0mm	Black Plated	10 mtrs	160 kgs
BC60BZP	6.0mm	42.0mm	13.0mm	Bright Zinc Plated	10 mtrs	160 kgs
BC60HDG	6.0mm	42.0mm	13.0mm	Hot Dip Galvanised	10 mtrs	160 kgs
BA70BLK	7.0mm	28.0mm	14.0mm	Black Plated	10 mtrs	220 kgs
BA70BZP	7.0mm	28.0mm	14.0mm	Bright Zinc Plated	10 mtrs	220 kgs
BA70HDG	7.0mm	28.0mm	14.0mm	Hot Dip Galvanised	10 mtrs	220 kgs
BC70BLK	7.0mm	49.0mm	14.0mm	Black Plated	10 mtrs	220 kgs
BC70BZP	7.0mm	49.0mm	14.0mm	Bright Zinc Plated	10 mtrs	220 kgs
BC70HDG	7.0mm	49.0mm	14.0mm	Hot Dip Galvanised	10 mtrs	220 kgs
BA80BLK	8.0mm	32.0mm	16.0mm	Black Plated	10 mtrs	320 kgs
BA80BZP	8.0mm	32.0mm	16.0mm	Bright Zinc Plated	10 mtrs	320 kgs
BA80HDG	8.0mm	32.0mm	16.0mm	Hot Dip Galvanised	10 mtrs	320 kgs
BC80BLK	8.0mm	52.0mm	16.0mm	Black Plated	10 mtrs	320 kgs
BC80BZP	8.0mm	52.0mm	16.0mm	Bright Zinc Plated	10 mtrs	320 kgs
BC80HDG	8.0mm	52.0mm	16.0mm	Hot Dip Galvanised	10 mtrs	320 kgs
BA100BLK	10.0mm	40.0mm	20.0mm	Black Plated	10 mtrs	350 kgs
BA100BZP	10.0mm	40.0mm	20.0mm	Bright Zinc Plated	10 mtrs	350 kgs
BA100HDG	10.0mm	40.0mm	20.0mm	Hot Dip Galvanised	10 mtrs	350 kgs
BC100BLK	10.0mm	65.0mm	20.0mm	Black Plated	10 mtrs	350 kgs
BC100BZP	10.0mm	65.0mm	20.0mm	Bright Zinc Plated	10 mtrs	350 kgs
BC100HDG	10.0mm	65.0mm	20.0mm	Hot Dip Galvanised	10 mtrs	350 kgs

Please call if you require longer lengths, or if you have a project where you require chains to be supplied to a specified length.

WELDED LINK CHAIN IN HANKS -DIN5685 SPECIFICATION

CPL Product Code	Material Dia	Inside Length	Inside Width	Surface Finish	Hanked Length	Max. Rec. Load
HA20BLK30	2.0mm	12.0mm	5.0mm	Black Plated	10 mtrs	20 kgs
HA20BZP30	2.0mm	12.0mm	5.0mm	Bright Zinc Plated	10 mtrs	20 kgs
HA20HDG30	2.0mm	12.0mm	5.0mm	Hot Dip Galvanised	10 mtrs	20 kgs
HC20BLK30	2.0mm	22.0mm	4.0mm	Black Plated	30 mtrs	20 kgs
HC20BZP30	2.0mm	22.0mm	4.0mm	Bright Zinc Plated	30 mtrs	20 kgs
HC20HDG30	2.0mm	22.0mm	4.0mm	Hot Dip Galvanised	30 mtrs	20 kgs
HA25BLK30	2.5mm	14.0mm	5.0mm	Black Plated	30 mtrs	30 kgs
HA25BRS30	2.5mm	14.0mm	5.0mm	Brass Plated	30 mtrs	30 kgs
HA25BZP30	2.5mm	14.0mm	5.0mm	Bright Zinc Plated	30 mtrs	30 kgs
HA25HDG30	2.5mm	14.0mm	5.0mm	Hot Dip Galvanised	30 mtrs	30 kgs
HC25BLK30	2.5mm	24.0mm	5.0mm	Black Plated	30 mtrs	30 kgs
HC25BZP30	2.5mm	24.0mm	5.0mm	Bright Zinc Plated	30 mtrs	30 kgs
HC25HDG30	2.5mm	24.0mm	5.0mm	Hot Dip Galvanised	30 mtrs	30 kgs
HA30BLK30	3.0mm	16.0mm	8.0mm	Black Plated	30 mtrs	40 kgs
HA30BZP30	3.0mm	16.0mm	8.0mm	Bright Zinc Plated	30 mtrs	40 kgs
HA30HDG30	3.0mm	16.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
HB30BLK30	3.0mm	21.0mm	8.0mm	Black Plated	30 mtrs	40 kgs
HB30BRS30	3.0mm	21.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
HB30BZP30	3.0mm	21.0mm	8.0mm	Bright Zinc Plated	30 mtrs	40 kgs
HB30HDG30	3.0mm	21.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
HC30BLK30	3.0mm	26.0mm	8.0mm	Black Plated	30 mtrs	40 kgs
HC30BZP30	3.0mm	26.0mm	8.0mm	Bright Zinc Plated	30 mtrs	40 kgs
HC30HDG30	3.0mm	26.0mm	8.0mm	Hot Dip Galvanised	30 mtrs	40 kgs
HA40BLK30	4.0mm	19.0mm	9.0mm	Black Plated	30 mtrs	80 kgs
HA40BZP30	4.0mm	19.0mm	9.0mm	Bright Zinc Plated	30 mtrs	80 kgs
HA40HDG30	4.0mm	19.0mm	9.0mm	Hot Dip Galvanised	30 mtrs	80 kgs
HC40BLK30	4.0mm	32.0mm	9.0mm	Black Plated	30 mtrs	80 kgs
HC40BZP30	4.0mm	32.0mm	9.0mm	Bright Zinc Plated	30 mtrs	80 kgs
HC40HDG30	4.0mm	32.0mm	9.0mm	Hot Dip Galvanised	30 mtrs	80 kgs
HA50BLK30	5.0mm	21.0mm	11.0mm	Black Plated	30 mtrs	125 kgs
HA50BZP30	5.0mm	21.0mm	11.0mm	Bright Zinc Plated	30 mtrs	125 kgs
HA50HDG30	5.0mm	21.0mm	11.0mm	Hot Dip Galvanised	30 mtrs	125 kgs
HC50BLK30	5.0mm	35.0mm	11.0mm	Black Plated	30 mtrs	125 kgs
HC50BZP30	5.0mm	35.0mm	11.0mm	Bright Zinc Plated	30 mtrs	125 kgs
HC50HDG30	5.0mm	35.0mm	11.0mm	Hot Dip Galvanised	30 mtrs	125 kgs

Continued.....



WELDED LINK CHAIN IN HANKS-DIN5685 SPECIFICATION

CPL Product Code	Material Dia	Inside Length	Inside Width	Surface Finish	Hanked Length	Max. Rec. Load
HA60BLK20	6.0mm	24.0mm	13.0mm	Black Plated	20mtrs	160 kgs
HA60BZP20	6.0mm	24.0mm	13.0mm	Bright Zinc Plated	20 mtrs	160 kgs
HA60HDG20	6.0mm	24.0mm	13.0mm	Hot Dip Galvanised	20 mtrs	160 kgs
HB60BLK20	6.0mm	33.0mm	13.0mm	Black Plated	20 mtrs	160 kgs
HB60BZP20	6.0mm	33.0mm	13.0mm	Bright Zinc Plated	20 mtrs	160 kgs
HB60HDG20	6.0mm	33.0mm	13.0mm	Hot Dip Galvanised	20 mtrs	160 kgs
HC60BLK20	6.0mm	42.0mm	13.0mm	Black Plated	20 mtrs	160 kgs
HC60BZP20	6.0mm	42.0mm	13.0mm	Bright Zinc Plated	20 mtrs	160 kgs
HC60HDG20	6.0mm	42.0mm	13.0mm	Hot Dip Galvanised	20 mtrs	160 kgs
HA70BLK15	7.0mm	28.0mm	14.0mm	Black Plated	15 mtrs	220 kgs
HA70BZP15	7.0mm	28.0mm	14.0mm	Bright Zinc Plated	15 mtrs	220 kgs
HA70HDG15	7.0mm	28.0mm	14.0mm	Hot Dip Galvanised	15 mtrs	220 kgs
HC70BLK15	7.0mm	49.0mm	14.0mm	Black Plated	15 mtrs	220 kgs
HC70BZP15	7.0mm	49.0mm	14.0mm	Bright Zinc Plated	15 mtrs	220 kgs
HC70HDG15	7.0mm	49.0mm	14.0mm	Hot Dip Galvanised	15 mtrs	220 kgs
HA80BLK15	8.0mm	32.0mm	16.0mm	Black Plated	15 mtrs	320 kgs
HA80BZP15	8.0mm	32.0mm	16.0mm	Bright Zinc Plated	15 mtrs	320 kgs
HA80HDG15	8.0mm	32.0mm	16.0mm	Hot Dip Galvanised	15 mtrs	320 kgs
HC80BLK15	8.0mm	52.0mm	16.0mm	Black Plated	15 mtrs	320 kgs
HC80BZP15	8.0mm	52.0mm	16.0mm	Bright Zinc Plated	15 mtrs	320 kgs
HC80HDG15	8.0mm	52.0mm	16.0mm	Hot Dip Galvanised	15 mtrs	320 kgs
HA100BLK15	10.0mm	40.0mm	20.0mm	Black Plated	15 mtrs	350 kgs
HA100BZP15	10.0mm	40.0mm	20.0mm	Bright Zinc Plated	15 mtrs	350 kgs
HA100HDG15	10.0mm	40.0mm	20.0mm	Hot Dip Galvanised	15 mtrs	350 kgs
HC100BLK15	10.0mm	65.0mm	20.0mm	Black Plated	15 Mtrs	350 kgs
HC100BZP15	10.0mm	65.0mm	20.0mm	Bright Zinc Plated	15 mtrs	350 kgs
HC100HDG15	10.0mm	65.0mm	20.0mm	Hot Dip Galvanised	15 mtrs	350 kgs

Please call if you require longer lengths, or if you have a project where you require chains to be supplied to a specified length.