

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19001-0006](#)  
**Status:** **Active**  
**Description:** Avikrimp™ Quick Disconnect, Male, for 14-16 (2.00-1.30mm<sup>2</sup>), Box, Tab 6.35 x 0.81mm

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-014 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-013 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
TUV R9071070  
UL E79133

**General**

Product Family Quick Disconnects  
Series [19001](#)  
Crimp Quality Equipment Yes  
Insulated Fully  
Product Name Avikrimp™  
Type Quick Disconnect  
UPC 800753026582

**Physical**

Barrel Type Closed  
Color - Resin Blue  
Flammability 94V-2  
Gender Male  
Glow-Wire Compliant No  
Insulation Nylon (PA)  
Lock to Mating Part None  
Material - Metal Brass  
Material - Plating Mating Zinc Chromate  
Material - Plating Termination Zinc Chromate  
Net Weight 1.658/g  
Orientation Straight  
Packaging Type Bag  
Plating min - Mating 5.080µm  
Plating min - Termination 5.080µm  
Polarized to Mating Part No  
Tab Thickness 0.81mm  
Tab Width 6.35mm  
Temperature Range - Operating -65°C to +105°C  
Wire Insulation Diameter 4.32mm max.  
Wire Size AWG 14, 16  
Wire Size mm<sup>2</sup> 1.30 - 2.00

**Electrical**

Voltage - Maximum 300V

**Material Info**

Old Part Number BB-5262

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013, PS-19902-014  
Sales Drawing SD-19001-003




image - Reference only

Series

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

19001Series

**Use With**

19002-0024 , 19002-0025 , 19002-0027

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0640012600</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640052600</a>

This document was generated on 05/15/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**