

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50058-8000](#)
Status: **Active**
Overview: [PicoBlade™ Connector System](#)
Description: 1.25mm Pitch PicoBlade™ Crimp Terminal, Female, 28-32 AWG, Reel

Documents:

3D Model	Product Specification PS-51021-022 (PDF)
Drawing (PDF)	Product Specification PS-51021-023 (PDF)
Product Specification PS-51021-001 (PDF)	Product Specification PS-51021-024 (PDF)
Product Specification PS-51021-002 (PDF)	Product Specification PS-51021-026 (PDF)
Product Specification PS-51021-009 (PDF)	Product Specification PS-51021-027 (PDF)
Product Specification PS-51021-010 (PDF)	Product Specification PS-51021-028 (PDF)
Product Specification PS-51021-011 (PDF)	RoHS Certificate of Compliance (PDF)




image - Reference only

General

Product Family	Crimp Terminals
Series	50058
Application	Signal
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	PicoBlade™ Connector System
Packaging Alternative	50058-8100 (Loose)
Product Name	PicoBlade™
UPC	800753576315

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	12.600/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.00mm
Wire Size AWG	28, 30, 32
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Product Specification	PS-51021-001, PS-51021-002, PS-51021-009, PS-51021-010, PS-51021-011, PS-51021-022, PS-51021-023, PS-51021-024, PS-51021-026, PS-51021-027, PS-51021-028, RPS-501576-001, RPS-51021-001, RPS-51021-002, RPS-51021-003, RPS-51021-004, RPS-51021-006, RPS-51021-007, RPS-51021-008, RPS-51021-009, RPS-51021-010, RPS-51021-011, RPS-51021-013, RPS-51021-014, RPS-51021-015, RPS-51021-016, RPS-51021-017, RPS-51021-018, RPS-51021-019, RPS-51021-020,
-----------------------	---

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50058Series

Mates With

50125 Crimp Terminal 26-28 AWG, [50133](#)
 Crimp Terminal 28-32 AWG

Use With

51021 PicoBlade™ Wire-to-Wire and Wire-to-Board Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	0638190300

RPS-51021-021, RPS-51021-022, RPS-51021-023,
RPS-51021-024, RPS-51021-025, RPS-51021-026,
RPS-51021-027, RPS-51021-028, RPS-51021-029,
RPS-51021-030, RPS-51021-031, RPS-51021-032,
RPS-51021-033, RPS-51021-034, RPS-51021-037,
RPS-51021-038, RPS-51021-039, RPS-51021-040,
RPS-51021-041, RPS-51021-042, RPS-51021-043,
RPS-51021-044, RPS-51021-045, RPS-51021-046,
RPS-51021-047, RPS-51021-048, RPS-51021-050,
RPS-51021-051, RPS-51021-052, RPS-51021-053,
RPS-51021-054, RPS-51021-055, RPS-51021-056,
RPS-51021-057, RPS-51021-058, RPS-51021-059,
RPS-51021-060, RPS-51021-061, RPS-51021-062,
RPS-51021-063, RPS-51021-064, RPS-51021-065,
RPS-51021-066, RPS-51021-067, RPS-51021-068,
RPS-51021-071, RPS-51021-072, RPS-51021-073,
RPS-51021-074, RPS-51021-076, RPS-51021-077,
RPS-51021-078, RPS-51021-079, RPS-51021-080,
RPS-51021-083, RPS-51021-084, RPS-51021-085,
RPS-51021-086, RPS-51021-089, RPS-51021-091,
RPS-51021-092, RPS-51021-096, RPS-51021-097,
RPS-51021-101, RPS-51021-102, RPS-51021-103,
RPS-51021-104, RPS-51021-105, RPS-51021-106,
RPS-51021-107, RPS-51021-108, RPS-51021-110,
RPS-51021-112, RPS-51021-117, RPS-51021-118,
RPS-51021-121, RPS-51021-122, RPS-53398-002,
RPS-53398-037, RPS-53398-038, RPS-53398-039
SD-50058-8*00

Sales Drawing

Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	<u>0638190400</u>
T2 Terminator	<u>0639103700</u>
Tooling Die	
FineAdjust™	<u>0639003700</u>
1.25mm Pitch Crimp Terminal, 26-32 AWG	
Hand Crimp Tool	<u>0638110000</u>
Terminals on Metal Strip	
Extraction Tool	<u>0011030043</u>
Japan	
Description	Product #
Applicator for M21 1A Bench Press, 26-32 AWG Wire	<u>0570673000</u>
Side-Feed Applicator For Full-Auto Machine	
Extraction Tool	<u>0570726000</u>

This document was generated on 06/05/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION