


**KEMET Part Number: PME295RB4470MR30**  
(P295BQ472M440A)

Capacitor, film, 4700 pF, +/-20% Tol, -40/+115C, Safety: Y1, 480VAC, Lead Spacing=15 mm



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	18	MAX
H	16	MAX
T	8.5	MAX
S	15	+/-0.4
LL	30	+5
G	0.5	NOM
F	0.8	+/-0.05

**Packaging Specifications**

Package Kind:	Bulk
Package Quantity:	400

**General Information**

Supplier:	KEMET
-----------	-------

**Specifications**

Capacitance:	4700 pF
Rated Temperature:	115C
Voltage AC:	480VAC
Tolerance:	+/-20%
Body Type:	Radial Box
Dielectric:	Metallized Paper
Application:	Safety: Y1
Temperature Range:	-40/+115C
Electrical Name (Other):	Self Resonant Frequency
Electrical Value (Other):	22
Electrical Units (Other):	MHz
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	2000 v/us

**Agency Approvals**

Approvals:	ENEC,UL,cUL
------------	-------------