

86 03 400



Pliers Wrench XL pliers and a wrench in a single tool



- for large screw joints also with pressure-sensitive surfaces such as plastic, copper, brass, stainless steel and chrome
- adjustable tightening tool
- replaces diverse expensive, large open-end wrenches up to AF 85 mm or 3 3/8"
- also excellent for gripping, holding, pressing and bending workpieces
- smooth jaws, also for gentle installation of quality union joints made from brass, red brass or stainless steel
- zero backlash jaw pressure prevents damage to edges of sensitive components
- adjustment at the touch of a button directly on the workpiece
- parallel jaws give a more solid grip; the construction gives infinite adjustment of all widths up to the specified maximum size
- optimised adjustment to the workpiece with hand-friendly position of grips
- reliable catching of the hinge bolt: no unintentional shifting
- the action of the jaws allows quick tightening and release of bolted connections using the ratchet principle
- lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

Open-end wrenches with fixed opening widths are expensive, especially when used for large union joints. The KNIPEX Pliers Wrench XL , with their adjustable jaw opening up to AF 85 mm / 3 3/8", offer enormous savings potential here.

Article No.	86 03 400
EAN	4003773077312
Pliers	nickel plated
Handles	plastic coated
B2 mm	16
B3 mm	20
B1 mm	12,5
Adjustment positions	25
Capacities for nuts Inch	3 3/8
Capacities for nuts mm	85
Working capacities Inch	3 3/8
Working capacities mm	85
Length mm	400
Net weight g	1460



technical change and errors excepted

