

# Bulb Overview



	PART NO.	DESCRIPTION	TOTAL LENGTH(mm)	VOLTAGE	FOR USE WITH:												
	<b>955 840 34</b>	Bulb BA15d 5 W	42	12 V	200	203	209	641	800	840	845						
	<b>955 840 35</b>	Bulb BA15d 5 W	42	24 V	200	203	209	641	800	840	845						
	<b>955 840 32</b>	Bulb BA15d 5 W	42	30 V	200	203	209	641	800	840	845						
	<b>955 840 57</b>	Bulb BA15d 5 W	42	115 V	200	203	209	641	800	840	845						
	<b>955 840 38</b>	Bulb BA15d 5 W	42	230 V	200	203	209	641	800	840	845						
	<b>955 015 34</b>	Bulb BA15d 7 W	52	12 V	210	213	219	220	480	580	815						850
	<b>955 015 35</b>	Bulb BA15d 7 W	52	24 V	210	213	219	220	480	580	815	826					850
	<b>955 015 36</b>	Bulb BA15d 7 W	52	48 V	210	213	219	220	480	580	815	monit.					850
	<b>955 015 37</b>	Bulb BA15d 7 W	52	115 V	210	213	219	220	480	580	815						850
	<b>955 015 38</b>	Bulb BA15d 7 W	52	230 V	210	213	219	220	480	580	815						850
	<b>955 826 35</b>	Bulb BA15d 15 W	45	24 V	826												
	<b>955 826 38</b>	Bulb BA15d 15 W	45	230 V	826												
	<b>955 827 35</b>	Bulb BA15d 25 W	55	24 V	827												
	<b>955 827 37</b>	Bulb BA15d 25 W	55	115 V	827												
	<b>955 827 38</b>	Bulb BA15d 25 W	55	230 V	827												
	<b>955 890 38</b>	Bulb E14 15 W	76	230 V	890	895											
	<b>955 880 66</b>	Bulb E14 40 W	76	48 V	881												
	<b>955 880 67</b>	Bulb E14 40 W	76	115 V	881												
	<b>955 880 68</b>	Bulb E14 40 W	76	230 V	881												

Minimal differences in form are possible within the different bulb models.

	PART NO.	DESCRIPTION	TOTAL LENGTH(mm)	VOLTAGE	FOR USE WITH:
	<b>955 890 55</b>	Bulb E27 25 W	100	24 V	890 895
	<b>955 890 67</b>	Bulb E27 25 W	100	115 V	890 895
	<b>955 890 68</b>	Bulb E27 25 W	100	230 V	890 895
	<b>955 883 34</b>	Halogen bulb G 6.35 35 W	40	12 V	783 784 883 884
	<b>955 883 35</b>	Halogen bulb G 6.35 35 W	40	24 V	783 784 883 884
	<b>955 885 24</b>	Halogen bulb G 6.35 20 W	40	12 V	783 885
	<b>955 885 25</b>	Halogen bulb G 6.35 20 W	40	24 V	783 885
	<b>955 880 34</b>	Halogen bulb H 1 55 W	57	12 V	880
	<b>955 880 35</b>	Halogen bulb H 1 70 W	57	24 V	880
	<b>956 x00 75</b>	LED bulb BA15d	42	24 V	200, 203, 206, 209, 210,
	<b>956 x00 67</b>	LED bulb BA15d	42	115 V	213, 216, 219, 220, 223,
	<b>956 x00 68</b> x see page 182	LED bulb BA15d	42	230 V	641, 805, 840, 846, 850, 851, 852
	<b>956 x20 75</b>	LED bulb E27	65	24 V	890 895
	<b>956 x20 67</b>	LED bulb E27	65	115 V	890 895
	<b>956 x20 68</b> x see page 183	LED bulb E27	65	230 V	890 895

Minimal differences in form are possible within the different bulb models.

