

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130058-0057](#)
Status: **Active**
Overview: Brad® Ethernet Solutions
Description: RJ-LNXX RJ45 Female to RJ45 Female Adaptor

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	130058
IP Rating	IP67
Overview	Brad® Ethernet Solutions
Product Name	RJ-Lnxx®
Type	In-Line Interconnect
UPC	78678850240

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	N/A
Material - Connector Body	Delrin
Material - Contact	N/A
Material - Coupling Nut	Nylon
Material - Plating Mating	n/a
Net Weight	42.568/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A

Electrical


Current - Maximum per Contact	1.5A
Voltage - Maximum	30V DC

Material Info

Old Part Number	RJBG16821
-----------------	-----------

Reference - Drawing Numbers

Sales Drawing	SD-130058-006
---------------	---------------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

130058Series