

Datasheet

Art.No. 80.020.2001.0

Solid state relay WRS-SSAC1-250V4A

WRS-solid-state-relays, 1-phase, solid state relay not plugable, with LED, open module housing WEB 1002, dimensions: 12,5 x 80 mm (WxH), control voltage: 24 V DC, output 250V AC / 4A (Remark: the negative pole can be linked At the controll side with A jumper to the next module , if needed it has to be ordered seperately).



Art.No.	80.020.2001.0
EAN	4015573322530
Order unit	10 pieces

Approvals



Technical data

General

Number of phases	1
Modular version	No

Technical data

Connection type	Screw connection
Type of excitation	
Min. connection voltage	48 V
Max. connection voltage	280 V
Rated operating current AC-1	4 A
Min. control voltage	24 V

Dimensions

Depth	56 mm
Width	12.5 mm
Height	80 mm