


Datasheet

Art.No. Z7.268.0227.0

Jumper bar IVB WKF 1,5- 2

Cross connector, insulated for DIN rail terminal blocks type WKF..., 2 -pole



Art.No.	Z7.268.0227.0
EAN	4015573732001
Order unit	10 pieces

Approvals

Technical data

General

Colour	Yellow
Type	Cross connector
Modular spacing	4.2 mm
Number of bridged clamps	2
Mounting method	Pluggable
Insulated	Yes

Accessories

Type	Cross connector
Mounting method	Pluggable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	2
Modular spacing	4.2 mm

Drawings

○ Diese Maßzahl ist bei diesem Insulator optional
○ Anzahl der Pole
○ M.F.P. (ANSI/IEEE) M.M. (UL) M.M. (IEC) M.M. (UL) M.M. (UL)

Z7.268.0227.0
M 1:1

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
i
11.1
12.1
1.1

Weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-number	Typ type	Polzahl pole	L
Z7.268.0227.0	IVB WKF 1,5- 2	2	7,0
Z7.268.0327.0	IVB WKF 1,5- 3	3	11,2
Z7.268.0427.0	IVB WKF 1,5- 4	4	15,4
Z7.268.0527.0	IVB WKF 1,5- 5	5	19,6
Z7.268.1027.0	IVB WKF 1,5-10	10	40,6
Z7.268.2027.0	IVB WKF 1,5-20	20	82,6

Freifertigkeit nach DIN		CAD - Zeichnung, keine manuellen Änderungen			1. Verwendung: -		Bl.: 1 von 1	
/ Maßstab		Werkstoff und Oberfläche:			/ Zeichnung Nr.		/ Index	
/ 5:1		2004 Tag			T		Z7.268.0227.0 01K	
/		Entworfen 09.11. Schnitt J.			/ Ersatz für -		/	
/		Geprüft -			/		/	
/		Nenngr. -			/		/	
/					/		/	
/		Typ IVB WKF 1,5-...			/		/	
/		Benennung VERBINDUNGSSTECKER insulated jumper bar			/		/	
/		Markenname / Defekt / Bestell Änderung			/		/	

Z7.268.0227.01K_4 DWK028 Schmitt 2004-11-09 10:33:52 1:000