


Datasheet

Art.No. Z7.268.1027.0

Jumper bar IVB WKF 1,5-10

Cross connector, insulated for DIN rail terminal blocks type WKF..., 10 -pole



Art.No.	Z7.268.1027.0
EAN	4015573732049
Order unit	10 pieces

Approvals

Technical data

General

Colour	Yellow
Type	Cross connector
Modular spacing	4.2 mm
Number of bridged clamps	10
Mounting method	Pluggable
Insulated	Yes

Accessories

Type	Cross connector
Mounting method	Pluggable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	10
Modular spacing	4.2 mm

Drawings

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
i
11.1
12.1
1.1

Z7.268.0227.0
 M 1:1

Weitere Daten siehe Katalog
 further data see catalog

Teile-Nr. part-number	Typ type	Polzahl pole	L
Z7.268.0227.0	IVB WKF 1,5- 2	2	7,0
Z7.268.0327.0	IVB WKF 1,5- 3	3	11,2
Z7.268.0427.0	IVB WKF 1,5- 4	4	15,4
Z7.268.0527.0	IVB WKF 1,5- 5	5	19,6
Z7.268.1027.0	IVB WKF 1,5-10	10	40,6
Z7.268.2027.0	IVB WKF 1,5-20	20	82,6

Freifertigkeit nach DIN

Maßstab: 5:1

Werkstoff und Oberfläche:

wieland

Wahlverfahre-
Verbindungen

Änderung

CAD - Zeichnung, keine manuellen Änderungen

2004 Tag: 09.11. Entworfen: Schmitt J. Geprüft: -

Benennung: Typ IVB WKF 1,5-..

1. Verwendung: -

Bl.: 1 von 1

Zeichnung Nr. T Z7.268.0227.0 01K

Ersatz für: -

Benennung: VERBINDUNGSSTECKER
insulated jumper bar

Z7.268.0227.01K_4 DWK028 Schmitt 2004-11-09 10:33:52 1:000