


Datasheet

Art.No. Z7.280.6327.0

Jumper bar IVBWKF 2,5 - 3

Cross connector, insulated for DIN rail terminal blocks type WKF..., 3 -pole



Art.No.	Z7.280.6327.0
EAN	4015573360143
Order unit	10 pieces

Approvals

Technical data

General

Colour	Yellow
Type	Cross connector
Modular spacing	5 mm
Number of bridged clamps	3
Mounting method	Pluggable
Insulated	Yes

Accessories

Type	Cross connector
Mounting method	Pluggable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	3
Modular spacing	5 mm

Drawings

**10-polige Ausführung
10 poles variant**

PA 66
UL 94 V-2

Teile-Nr. part nr.	Pol- zahl poles	L-0,2	l±0,05	Typ type
27.280.62MM.0	2			IVBKWF 2,5 - 2
27.280.63MM.0	3	14,8	10	IVBKWF 2,5 - 3
27.280.64MM.0	4	19,8	15	IVBKWF 2,5 - 4
27.280.65MM.0	5	24,8	20	IVBKWF 2,5 - 5
27.280.66MM.0	6	29,8	25	IVBKWF 2,5 - 6
27.280.67MM.0	7	34,8	30	IVBKWF 2,5 - 7
27.280.68MM.0	8	39,8	35	IVBKWF 2,5 - 8
27.280.69MM.0	9	44,8	40	IVBKWF 2,5 - 9
27.280.70MM.0	10	49,8	45	IVBKWF 2,5 - 10
27.280.71MM.0	11	54,8	50	IVBKWF 2,5 - 11
27.280.72MM.0	12	59,8	55	IVBKWF 2,5 - 12
27.280.73MM.0	13	64,8	60	IVBKWF 2,5 - 13
27.280.74MM.0	14	69,8	65	IVBKWF 2,5 - 14
27.280.75MM.0	15	74,8	70	IVBKWF 2,5 - 15
27.280.76MM.0	16	79,8	75	IVBKWF 2,5 - 16
27.280.77MM.0	17	84,8	80	IVBKWF 2,5 - 17
27.280.78MM.0	18	89,8	85	IVBKWF 2,5 - 18
27.280.79MM.0	19	94,8	90	IVBKWF 2,5 - 19
27.280.80MM.0	20	99,8	95	IVBKWF 2,5 - 20

MM	
27	Katalogteil catalogue part
97	spezielle Verpackung special packing

Freileitanz nach DIN CAD - Zeichnung, keine manuellen Änderungen 1. Verwendung: Bl.: 1 von 1

Maßstab	2001	Tag	Nr.	Zeichnung Nr.	Index
2:1	Entworfen	04.07.	TRESCHAN	27.280.6227.0 01K	a
	Geprüft	-	-		
	Montiert	-	-	Ersatz für:	

wieland **Typ** **Benennung**
 Industrietechnik IVB WK **VERBINDUNGSSTECKER**
 Verbindungen 2,5 - .. insulated jumper bar

Z:\280622701K_4_CAD\1032_Bauer_2005-07-28T14:14:24_1.000