


Datasheet

Art.No. Z7.268.2027.0

Jumper bar IVB WKF 1,5-20

Cross connector, insulated for DIN rail terminal blocks type WKF..., 20 -pole



Art.No.	Z7.268.2027.0
EAN	4015573732056
Order unit	10 pieces

Approvals

Technical data

General

Colour	Yellow
Type	Cross connector
Modular spacing	4.2 mm
Number of bridged clamps	20
Mounting method	Pluggable
Insulated	Yes

Accessories

Type	Cross connector
Mounting method	Pluggable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	20
Modular spacing	4.2 mm

Drawings

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
i
11.1
12.1
1.1

Insolierung
gelb/
insulation
yellow

Z7.268.0227.0
M 1:1

Weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-number	Typ type	Polzahl pole	L
Z7.268.0227.0	IVB WKF 1,5- 2	2	7,0
Z7.268.0327.0	IVB WKF 1,5- 3	3	11,2
Z7.268.0427.0	IVB WKF 1,5- 4	4	15,4
Z7.268.0527.0	IVB WKF 1,5- 5	5	19,6
Z7.268.1027.0	IVB WKF 1,5-10	10	40,6
Z7.268.2027.0	IVB WKF 1,5-20	20	82,6

Freifertiger nach DIN CAD - Zeichnung, keine manuellen Änderungen 1. Verwendung: - Bl.: 1 von 1

Maßstab	Werkstoff und Oberfläche:	2004	Tag	Name	Zeichnung Nr.
5:1		Entworfen	09.11.	Schnitt J.	T
		Geprüft	-	-	Z7.268.0227.0 01K
		Neugegr.	-	-	Ersatz für -

wieland
Markenname
Markenbezeichnungen

Typ
IVB
WKF 1,5-..

Benennung
VERBINDUNGSSTECKER
insulated jumper bar

Z7.268.0227.01K_4 DWK028 Schmitt 2004-11-09 10:33:52 1:000