

# Color-Keyed®

## Standard Barrel Copper Lug T&B Catalog Number:




54165-TB  
78621054165  
Active

**UPC Number:**  
**Status:**  
**Description:**

Copper One-Hole Lug - Straight Standard Barrel - max 35KV, 3/0 AWG Wire, 1/2" Bolt Size, Tin Plated with Inspection Hole, Orange 50

### General



Material	Copper
Finish	Tin Plated
Wire Size	3/0 AWG
Number of Studs	1
Stud Size	1/2
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Orange
Die Code	50

### Dimension Information

A (inches)	2.35
B (inches)	1.25
C (inches)	0.92
D (inches)	0.13
E (inches)	0.63
F (inches)	0.5

### Specifications

Voltage Rating	600V to 35KV
----------------	--------------

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	8.9 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00675-tb2
Overview	Available on Website

### Notes

Dimensions given for reference only. Dimensions may vary up to +/- .030.

### Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)