



Sample photo

**Order symbol:** AR664CHSCT  
**Product nbr:** 8561016  
**Description:** PC Enclosure  
**Remarks:** Hinged transparent screw cover

**EAN:** 6418074066480  
**EI. number:**  
 Finland:  
 Norway:

Including: Hinged screw cover base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		152	152	102	Ingress Protection (EN 60529): 66/67
<b>inch:</b>		6.0	6.0	4.0	Electrical insulation: Totally insulated
<b>Materials:</b>					Halogen free (DIN/VDE 0472, Part 815): yes
<b>Material:</b>		Polycarbonate			UV resistance: UL 508
<b>Base colour:</b>		RAL 7035 -light grey			Flammability Rating (UL 746 C 5): complies with UL 508
<b>Cover colour:</b>		Transparent cover			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Cover screws material:</b>		Stainless steel			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13
<b>Gasket material:</b>		Polyurethane			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 140 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 284 °F			
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
APBP66		PVC Back Panel			
ABP66		Painted Steel Back Panel			
ALBP66		Aluminum Back Panel			
ADFP66		Dead Front Panel w/ screws			
ASP66		Aluminum Swing Panel			
ASPK66		Swing Panel Kit incl. Panel			
ASPHK6		Swing Panel Kit w/o Panel			
AMFL6		6" Mounting Flange Set			

