



Sample photo

Order symbol: AR664CHSST
Product nbr: 8561051
Description: PC Enclosure
Remarks: Hinged transparent cover
w/S.S. Quick release latch

EAN: 6418074067074
EI. number:
Finland:
:
Norway:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Rating:
Length	Width	Height		
mm: 152	152	102		Ingress Protection (EN 60529): 66/67
inch: 6.0	6.0	4.0		Electrical insulation: Totally insulated
Materials:				Halogen free (DIN/VDE 0472, Part 815): yes
Material:	Polycarbonate			UV resistance: UL 508
Base colour:	RAL 7035 -light grey			Flammability Rating (UL 746 C 5): complies with UL 508
Cover colour:	Transparent cover			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws material:	Stainless steel			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13
Gasket material:	Polyurethane			Certificates:

Temperatures:	
Short term:	-40 ... 140 °C
Continuous:	-40 ... 80 °C
Short term:	-40 ... 284 °F
Continuous:	-40 ... 175 °F

Accessories:	
APBP66	PVC Back Panel
ABP66	Painted Steel Back Panel
ALBP66	Aluminum Back Panel
ADFP66	Dead Front Panel w/ screws
ASP66	Aluminum Swing Panel
ASPK66	Swing Panel Kit incl. Panel
ASPHK6	Swing Panel Kit w/o Panel
AMFL6	6" Mounting Flange Set

