



Sample photo

**Order symbol:** P 252612  
**Product nbr:** 7094370  
**Description:** Enclosure  
**Remarks:** Polyester

**EAN:** 6418074004420  
**EI. number:**  
Finland: 3423673  
Denmark: 8212005691  
Italy: 7331055  
Sweden: 2536231  
Norway:

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		256	251	121	Ingress Protection (EN 60529): IP 66
<b>inch:</b>		10.1	9.9	4.8	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polyester		Halogen free (DIN/VDE 0472, Part 815): Yes	
<b>Base colour:</b>		RAL 7001		UV resistance: UL 508	
<b>Cover colour:</b>		RAL 7001		Flammability Rating (UL 746 C 5): UL 746C 5V	
<b>Cover screws material:</b>		Stainless steel		Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Gasket material:</b>		EPDM		NEMA Class: NEMA 1, 4, 4X, 12, 13	
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-50 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-60 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
PM 2526		Mounting plate			
PRH 2526		DIN-35 Mounting rail			
MRS 28541		Wall fastening lug (2 pcs)			
PH A & AH A/B		Hinge set			

