



Sample photo

Order symbol: PC 081607
Product nbr: 7032620
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074003638
EI. number:
 Finland: 3423430
 Denmark: 8212002665
 Italy: 7301025
 Sweden: 2536113
 Norway: 2536607

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		160	80	65	Ingress Protection (EN 60529): IP 66/67
inch:		6.3	3.1	2.6	Impact Resistance (EN 62262): IK 08/07
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
TM 0816		Mounting plate			
TRM 0808		DIN-15 Mounting rail			
TRM 0816		DIN-15 Mounting rail			
TRH 1216		DIN-35 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			
Certificates:					
		Fimko			
		Europe EN 62208: 2003			
		Gost R			

