

SOLID PC 3828 13 T



Sample photo

Order symbol: PC 3828 13 T
Product nbr: 5330063
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005557
EI. number:
 Finland: 3423817
 Italy: 7402050
 Sweden: 2539452
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		378	278	130	Ingress Protection (EN 60529): IP 66/67
inch:		14.9	10.9	5.1	Impact Resistance (EN 62262): IK 08/09
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		Clear transparent		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Fimko	
Continuous:		-40 ... 80 °C		Europe EN 62208: 2003	
Short term:		-40 ... 250 °F		Gost R	
Continuous:		-40 ... 175 °F			
Accessories:					
EKPVT		Mounting plate			
EKPXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKPZR		Extension frame			

