

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [49702-6802](#)  
**Status:** **Active**  
**Description:** 2.28mm Tab-Type Female Crimp Terminal, Low Insertion Force Type, Middle Size, Tin Plated, AVSS (CAVS) 0.5, 0.85, 1.25mm<sup>2</sup>;

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-49702-001 \(PDF\)](#)  
[Product Specification PS-49006-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">49702</a>
Application	Power
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	822348108299


**Physical**

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.391/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.10-1.60mm
Wire Size AWG	16, 18, 20
Wire Size mm <sup>2</sup>	1.25-0.50

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-49702-001
Product Specification	PS-49006-001
Sales Drawing	SD-49702-001



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Contains SVHC: No**  
**Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[49702Series](#)

**Mates With**

[57919-6702](#)

**Use With**

[49009-4610](#)