



Black Box Products

Cables > Computer & Data Cables

RS-232 Extended-Distance/Quiet Cable with Molded Hoods, 4 Conductors (2 Pairs), Male/Male, Custom Lengths



Transmit RS-232 data up to 500 feet at 9600 bps!
EMN04C-MM
Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- Feature a foil shield plus an 85% tinned copper braid for extra protection against EMI/RFI transmissions in noisy office environments.
- Molded, nonremovable hoods.
- Guaranteed for life!



Description

RS-232 Extended-Distance/Quiet Cable with Molded Hoods, 4 Conductors (2 Pairs), M/M, Custom Lengths

Quick Facts

- Feature a foil shield plus an 85% tinned copper braid for extra protection against EMI/RFI transmissions in noisy office environments.
- Molded, nonremovable hoods.
- Guaranteed for life!

Further Details

- NEC® CL2 compliant. For connecting computers inside a building. Not for use in risers or plenums.
- Low capacitance.
- All conductors are straight wired for connecting the serial output of your computer to a switch box.
- Male screw locks are standard.
- Perfect for industrial applications near heavy machinery or in environments with high EMI/RFI. ED/Q cable features a stranded twisted-pair construction covered with two shields. A shorted aluminum-foil shield attenuates high-frequency emissions. A copper-braid shield attenuates low-frequency emissions.

Technical Specifications for RS-232 Extended-Distance/Quiet Cable with Molded Hoods, 4 Conductors (2 Pairs), Male/Male, Custom Lengths:

Cable Construction	PVC
Capacitance	12 pF/ft. ± 2 pF/ft.
Conductor Gauge	24 AWG (7 x 32), stranded
Outside Diameters	0.245", 0.260", 0.335", 0.365", 0.430
Resistance	30 ohms/1000 ft.

