

Small Hand Tools

★★ Two Stars

Scratch Brushes – Bench Brushes

Brass, Steel, Fiberglass and Nylon Bristles

264 ★★

Fiberglass Cleaning Brush

Refillable with long thin handle. Used in very confined areas, which are not accessible with larger diameter brushes. Overall length is 5 ¼" and ½" round. Brush is 1/20" diameter. For fiberglass refill, use reference no. 264A.



263 ★★


Fiberglass Scratch Brush

Retractable and refillable, with plastic handle. Very useful when cleaning and polishing. Overall length is 4 ¼" and ⅝" round. Brush is 5/16" diameter. Refills available. Use reference no. 263A.



Scratch Brushes

Retractable and refillable with plastic handle. Can be used for fine deburring, polishing, rust removal, or cleaning and erasing in chemical etching processes. Excellent for pre-solder and contact cleaning. Overall length is 4 ¾" and ⅜" round. Brush is 1/8" diameter.



REF. NO.	BRUSH MATERIAL	REFILL ONLY REF. NO.
265 ★★	Brass	265A
266 ★★	Steel	266A
267 ★★	Fiberglass	267A
268 ★★	Nylon	268A

Bench Brushes – Standard ESD Safe

Made of high grade bristles with a wooden handle. There are four rows of bristles 4 ½" long and ½" wide, which will not shed. Overall length is 10". Available in three degrees of hardness:

- 187 ★★ – Soft
- 189 ★★ – Half Soft
- 190 ★★ – Half Hard



262 ★★

Brush Kit

Kit consists of the following:
1 each brush holder, 265A brass refill, 266A steel refill, 267A fiberglass refill, 268A nylon refill. Supplied in plastic case.



186 ★★

Nylon Bench Brush

White Nylon bristles with a wooden handle. 4 rows of bristles 3 ¾" long and ½" wide. Overall length is 8 ½".



214-H★★

Applicator Brush

Double-ended applicator brush with a short flat end and an extra stiff chiseled end. Bristles are soft Horse Hair. Handle is 4 1/2" long and 3/16" diameter.



215-H★★

Applicator Brush

Double-ended applicator brush with a short flat end and an extra stiff chiseled end. Bristles are soft Horse Hair. Handle is 4 1/2" long and 3/8" diameter.

