



Your connection to electronic  
products and components

888.235.4692  
Mon-Fri 8-8, Sat 9-3et

## 16dB Fixed Mini-Type Attenuator Pad

MCM Part #: 33-2775 | Distributed By MCM Part #: FAM-16

Nickel-plated, solid brass body, monolithic ceramic printed circuit board, ensuring rugged construction, etched glaze-type resistors provide  $\pm 5\%$  accuracy and excellent return loss, small 1.375" size, 22-gauge spring steel center pin, female to male fitting, not DC passive.

### Specifications:

- Bandwidth: 100KHz~1750MHz
- Return loss: 20dB typical
- Accuracy:  $\pm 5\%$

