

★★★★★ **7000 Series Large Head Cutters**

Made in the U.S.A.



Edge hardened to 63/65 Rockwell “C”

Stainless steel leaf springs – Fine cutting of medium leads and wires

7100 Series Large Head Cutters with Long Foam Cushion Grips

6” Large Round Head Cutter


PART #	CUT TYPE	CUTTING CAPACITY
7150E	Semi-flush	.015” - .050”
7151E	Max flush	.012” - .050”
7152E	Opti-flush	.008” - .045”



7200 Series Large Head Cutters with ESD Safe Molded Grips

5 ¼” Large Round Head Cutter

PART #	CUT TYPE	CUTTING CAPACITY
7250E	Semi-flush	.015” - .050”
7251E	Max flush	.012” - .050”
7252E	Opti-flush	.008” - .045”



★★★★★ **7000 Series Parallel Jaw Cutters**


Made in the U.S.A.

Parallel jaw for cutting multiple leads and wires.

7100 Series Parallel Jaw Cutters with Long Foam Cushion Grips

6” Large Round Head Cutter

PART #	CUT TYPE	CUTTING CAPACITY
7150EM	Semi-flush	.015” - .050”
7151EM	Max flush	.012” - .050”
7152EM	Opti-flush	.008” - .045”



7200 Series Parallel Jaw Cutters with ESD Safe Molded Grips

5 ¼” Large Round Head Cutter

PART #	CUT TYPE	CUTTING CAPACITY
7250EM	Semi-flush	.015” - .050”
7251EM	Max flush	.012” - .050”
7252EM	Opti-flush	.008” - .045”

