



**LABOR
SAVING
DEVICES INC.**

Premium Flexible High-Speed Steel Drill Bits - The Best Bits for In-Wall Use

Professional installers consistently choose these drill bits above conventional bellhanger bits and other jobber bits for retrofit installation applications because of superior functionality, high quality construction and dependable performance. These bits have many features that make them your best choice for a wide variety of retrofit situations. High speed steel offers superior functionality. Manufactured in the U.S.A. by Freeform.

Features include:

- Designed to drill through steel plates as well as wood.
- 118 degree point provides more gradual breakthrough and limits the grabbing that occurs when using a traditional 135 degree point.
- Split point tip and slow spiral design improves bit self-cleaning and eases pull back.
- 3/16" flexible shaft allows you to easily align the bit along a stud for reference drilling.
- Holes in drill bit head and chuck end for attaching wire.



3/8" Bits:	Model Name	Part No:
3/8" x 18" Premium Freeform Bit	FF3818F	65-218
3/8" x 24" Premium Freeform Bit	FF3824F	65-224

3/8" x 36" Premium Freeform Bit	FF3836F	65-236
3/8" x 48" Premium Freeform Bit	FF3848F	65-248
3/8" x 58" Premium Freeform Bit	FF3858F	65-258
3/8" x 72" Premium Freeform Bit	FF3872F	65-272
1/2" Bits:	Model Name	Part No:
1/2" x 18" Premium Freeform Bit	FF1218F	65-318
1/2" x 24" Premium Freeform Bit	FF1224F	65-324
1/2" x 36" Premium Freeform Bit	FF1236F	65-336
1/2" x 48" Premium Freeform Bit	FF1248F	65-348
1/2" x 58" Premium Freeform Bit	FF1258F	65-358
1/2" x 72" Premium Freeform Bit	FF1272F	65-372