

DC Connector, Plug, 6.5x4.3 mm, 2-pole, angled, with cable



Description

- pre-assembled cable
- Low Voltage DC Plug and Socket
- DC Plug: 2-pole, angled

Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

Technical Data

Diameter	6.5 mm / 4.3 mm / 1.4 mm
Number of Poles	2-pole
Ratings DC	2A / 18VDC
Dielectric Strength	500VDC
Insulation Resistance	> 100 MΩ @ 500VDC

Allowable Operation Temp.	-20°C to 70°C
Terminal	Cable
Cord Length	1.8 m
Cable Cross Section	2 x 0.3 mm ²
Style	angled
Lifetime	5000 Insertions

Dimensions



All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
DC Plug/Socket	6.5	2-pole	Cable	4840.5231

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Outlets/Connectors

Category / Description

[DC Plug/Socket Overview complete](#)

4840, solder terminal, , Socket, 7.0 mm, 2-pole, DC Plug/Socket

[4840.2230](#)

4840, PCB terminals, , Socket, 7.0 mm, 2-pole, DC Plug/Socket

[4840.2232](#)[DC Plug/Socket further types to 4840 DC-Stecker, verschiedene](#)