


FILE NO. 36-460


THIS DRAWING AND SPECIFICATIONS, HEREIN ARE THE CONFIDENTIAL PROPERTY OF SAMAR AND SHALL NOT BE REPRODUCED OR COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION.

REV.	DESCRIPTION	DRAWN / DATE	APPROVED / DATE
0	INITIAL RELEASE	FROS 03/20/2014	FROS 03/20/2014



DESCRIPTION:

1. CONDUCTOR: 0.16MM/7 (BARE COPPER)X 4C
2. COLOR CODED INSULATION: (PP) BLACK, RED, GREEN, YELLOW
3. COLOR JACKET: (PVC) SILVER GRAY
4. ID: 0.95±0.05MM, OD: 2.4X4.9MM±0.1
5. LENGTH: 1000FT
6. TEMPERATURE: 60°C TO 10°C
7. VOLTAGE RATING: 150V



ELECTRICAL PROPERTIES:


TENSILE STRENGTH:

1. INSULATION: MIN 1.0KG/MM²
2. JACKET: MIN 1.3KG/MM²

ELONGATION:

1. INSULATION: MIN 200%
2. JACKET: MIN 100%

CONDUCTOR RESISTANCE: 45.2Ω/ KFT AT 20°C
 INSULATION RESISTANCE: MIN 45.3MΩ/ KFT AT 20°C
 DIELECTRIC WITHSTAND: AC1500V/ MIN AT 20°C



DIMENSIONS ARE IN mm [INCH]		TOLERANCES ARE FRACTIONS DECIMALS ANGLES		MATERIAL	FLAT TYPE 4C TELEPHONE WIRE, 100FT	P/N 36-460		DRAWN FROS	DATE 03/20/2014
MOLD NO.		.x ± 0.20 [0.008]		FINISH		PROJECT NO.			
36-460		.xx ± 0.12 [0.005]		COLOR		SCALE N/A	SIZE A4	SHEET 1 OF 1	MN010