



FILE NO. 36-615

THIS DRAWING AND SPECIFICATIONS, HEREIN ARE THE CONFIDENTIAL PROPERTY OF SAMAR AND SHALL NOT BE REPRODUCED OR COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION.

REV.	DESCRIPTION	DRAWN / DATE	APPROVED / DATE
0	INITIAL RELEASE	YANG 07/10/2014	FROS 07/10/2014



DESCRIPTION:

1. CONDUCTOR: 0.16MM/7 (BARE COPPER)X 6C
2. COLOR CODED INSULATION: (PP) WHITE, BLACK, RED, GREEN, YELLOW, BLUE
3. COLOR JACKET: (PVC) SILVER GRAY
4. ID: 0.95±0.05MM, OD: 2.4X6.7MM±0.1
5. LENGTH: 100FT

ELECTRICAL PROPERTIES:

TENSILE STRENGTH:

1. INSULATION: MIN 1.0KG/mm<sup>2</sup>
2. JACKET: MIN 1.3KG/mm<sup>2</sup>


ELONGATION:

1. INSULATION: MIN 200%
2. JACKET: MIN 100%

CONDUCTOR RESISTANCE: 45.2Ω/KFT (AT 20°C)

INSULATION RESISTANCE: MIN 45.3MΩ/KFT (AT 20°C)

DIELECTRIC WITHSTAND: AC1500V/MIN (AT 20°C)



DIMENSIONS ARE IN mm [INCH]	TOLERANCES ARE FRACTIONS DECIMALS ANGLES	MATERIAL	P/N	36-615	DRAWN	YANG	DATE	07/10/2014
MOLD NO.	.x ± 0.20 [0.008] .xx ± 0.12 [0.005]	FINISH	PROJECT NO.					
36-615		COLOR	SCALE	N/A	SIZE	A4	SHEET	1 OF 1
			6C 100ft telephone wire			MN010		