



# M22 Connectors – Polarised

## Latched Female Crimp Housing and Contacts

- Female crimp housings latch into male shrouded PC tail connectors.
- Mates with male connectors shown on page 137.




### CRIMP HOUSING




### CALCULATION

<b>A</b>	$B + 3.80$
<b>B</b>	$2.00 \times (\text{No. of contacts per row} - 1)$

### CRIMP CONTACT



- Order codes for reeled contacts refer to one reel of 10,000 contacts.
- Order codes for loose contacts refer to one pack of 100 contacts.
- Crimp contact suitable for 24 to 30 AWG.



Wire stripping details

### HAND CRIMP TOOL



### ORDER CODE

722-020

Instruction sheets available at [www.harwin.com/downloads/instructions](http://www.harwin.com/downloads/instructions)

### HOW TO ORDER

**M22 - 30 X XX XX**

#### SERIES CODE

#### CONNECTOR TYPE

<b>6</b>	Reeled Contact
<b>7</b>	Crimp Housing
<b>8</b>	Loose Contact

#### FINISH

<b>00</b>	Housing	PG
<b>46</b>	Tin (Contacts)	PG

#### NO. OF CONTACTS PER ROW

<b>02 to 15</b>	Housing
<b>00</b>	Contacts

All dimensions in mm.

2mm (.079") PITCH