





# IC Sockets

## Dual Row IC Socket

- Socket accepts IC leads  $\varnothing 0.41$  to  $0.56\text{mm}$ .
- End and side stackable.
- Utilises four finger Beryllium Copper contact technology (see the Datamate range for more detail).
- Please consult drawings for specifications.



### IC SOCKET



Recommended PC Board Pattern

A	B	C	D	No. OF CONTACTS	ORDER CODE
7.60	5.08	10.02	7.62 (0.3")	6	<b>D2806-42</b>
10.10	7.62	10.02	7.62 (0.3")	8	<b>D2808-42</b>
17.70	15.24	10.02	7.62 (0.3")	14	<b>D2814-42</b>
20.30	17.78	10.02	7.62 (0.3")	16	<b>D2816-42</b>
22.80	20.32	10.02	7.62 (0.3")	18	<b>D2818-42</b>
25.30	22.86	10.02	7.62 (0.3")	20	<b>D2820-42</b>
27.80	25.40	10.02	7.62 (0.3")	22	<b>D2922-42</b>
27.80	25.40	12.60	10.16 (0.4")	22	<b>D2822-42</b>

A	B	C	D	No. OF CONTACTS	ORDER CODE
30.40	27.94	10.02	7.62 (0.3")	24	<b>D2924-42</b>
30.40	27.94	12.60	10.16 (0.4")	24	<b>D2724-42</b>
30.40	27.94	17.64	15.24 (0.6")	24	<b>D2824-42</b>
35.50	33.02	10.02	7.62 (0.3")	28	<b>D2928-42</b>
35.50	33.02	17.64	15.24 (0.6")	28	<b>D2828-42</b>
40.60	38.10	17.64	15.24 (0.6")	32	<b>D2832-42</b>
50.80	48.26	17.64	15.24 (0.6")	40	<b>D2840-42</b>
60.90	58.42	17.64	15.24 (0.6")	48	<b>D2948-42</b>
81.2	78.74	25.4	22.86 (0.9")	64	<b>D2864-42</b>

### HOW TO ORDER

**D2 XXX - 42**

**SERIES CODE**

**TYPE**

See table above

**FINISH**

42 Gold + Tin



All dimensions in mm.