

## Coupler connector - SH-8EPS48A9LDLS - 1621554

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Coupling connector, straight long, shielded: Yes, SPEEDCON locking, M23, Number of positions: 8+4+PE, Type of contact: Male connector, Crimp connection, Cable diameter: 7.5 mm ... 18 mm

The figure shows the product version with CAT5 interface



### Key commercial data

Packing unit	1
GTIN	 4 046356 937023
Custom tariff number	85366990

### Technical data

Product type	Circular connector (cable-side)
Cable diameter	7.5 mm ... 18 mm
Coding	N
Type	Coupling connector
Number of positions	13
Thread	M23
Rated voltage (IEC)	630
Rated current (IEC)	30
Knurl material	Metal
Shielding	Yes
Signal type	Hybrid
Connection method	Crimp connection

### Classifications

eCl@ss

eCl@ss 5.1	27260701
eCl@ss 8.0	27440102

# Coupler connector - SH-8EPS48A9LDLS - 1621554


## Classifications

ETIM


ETIM 4.0	EC002635
ETIM 5.0	EC002635

## Drawings

Schematic diagram



Dimensioned drawing



Pin assignment of pin, signal

Pin version: dimension A = 4.7 mm, socket version: dimension A = 0 mm