

Cable connector - SH-8EPS48A8LDLS - 1621534

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable connector, straight long, shielded: Yes, SPEEDCON locking, M23, Number of positions: 8+4+PE, Type of contact: Male connector, Crimp connection, Cable diameter: 7.5 mm ... 18 mm

The figure shows the product version with CAT5 interface



Key commercial data

Packing unit	1
GTIN	 4 046356 936576
Custom tariff number	85366990

Technical data

Product type	Circular connector (cable-side)
Cable diameter	7.5 mm ... 18 mm
Coding	N
Type	Cable connector
Number of positions	13
Thread	M23
Rated voltage (IEC)	630
Rated current (IEC)	30
Knurl material	Metal
Shielding	Yes
Signal type	Hybrid
Connection method	Crimp connection

Classifications

eCl@ss

eCl@ss 5.1	27260701
eCl@ss 8.0	27440102

Cable connector - SH-8EPS48A8LDLS - 1621534


Classifications

ETIM

ETIM 4.0	EC002635
ETIM 5.0	EC002635


Drawings

Schematic diagram



Pin assignment of pin, signal

Dimensioned drawing



Pin version: dimension A = 0.2 mm, socket version: dimension A = 0 mm