

Coupler connector - SH-8ESC58A9LDLS - 1621539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Coupling connector, straight long, shielded: Yes, SPEEDCON locking, M23, Number of positions: 4+4+4+PE, Type of contact: Socket, Crimp connection, Cable diameter: 7.5 mm ... 18 mm



Key commercial data

Packing unit	1
GTIN	4 046356 936873
Custom tariff number	85366990

Technical data

Product type	Circular connector (cable-side)
Cable diameter	7.5 mm ... 18 mm
Coding	N
Type	Coupling connector
Number of positions	13
Thread	M23
Rated voltage (IEC)	630
Rated current (IEC)	30
Knurl material	Metal
Shielding	Yes
Signal type	Hybrid
Connection method	Crimp connection

Classifications

eCl@ss

eCl@ss 5.1	27260701
eCl@ss 8.0	27440102

Coupler connector - SH-8ESC58A9LDLS - 1621539


Classifications

ETIM


ETIM 4.0	EC002635
ETIM 5.0	EC002635

Drawings

Schematic diagram



Dimensioned drawing



Socket pin assignment, CAT5

Pin version: dimension A = 4.7 mm, socket version: dimension A = 0 mm