


## Crimp contact - ST-10KP020 - 1618256

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.34 mm<sup>2</sup>...0.5 mm<sup>2</sup>

### Key commercial data

Packing unit	100 pc
Minimum order quantity	10 pc
GTIN	 4 046356 736442
Weight per Piece (excluding packing)	0.35 g
Custom tariff number	85369010
Country of origin	Germany
Product key	ABREBC
Note	Made to Order (non-returnable)

### Technical data

#### General

Contact type	turned
Contact diameter	1 mm
Contact type	Male connector
Connection type	Crimp connection
Litz wire cross section min.	0.34 mm <sup>2</sup>
Litz wire cross section max.	0.5 mm <sup>2</sup>

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312

# Crimp contact - ST-10KP020 - 1618256

## Classifications

### eCl@ss

eCl@ss 8.0	27440312
------------	----------

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

GOST 
--