

Crimp contact - ST-10KS020 - 1618251


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.34 mm²...0.5 mm²



Key commercial data

Packing unit	100 pc
Minimum order quantity	10 pc
GTIN	 4 046356 736411
Weight per Piece (excluding packing)	0.29 g
Custom tariff number	85369010
Country of origin	Germany
Product key	ABREBC
Note	Made to Order (non-returnable)

Technical data

General

Contact type	turned
Contact diameter	1 mm
Contact type	Socket
Connection type	Crimp connection
Litz wire cross section min.	0.34 mm ²
Litz wire cross section max.	0.5 mm ²

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701

Crimp contact - ST-10KS020 - 1618251

Classifications

eCl@ss

eCl@ss 5.1	27141190
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals


Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 

Drawings

Crimp contact - ST-10KS020 - 1618251

Dimensioned drawing

