

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [39530-0006](#)  
**Status:** **Active**  
**Description:** 5.08mm Pitch Eurostyle™ Horizontal Plug, 6 Circuits

**Documents:**

[3D Model](#) [Product Specification PS-39500-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Terminal Blocks
Series	<a href="#">39530</a>
Application	N/A
Component Type	Plug
MolexKits	Yes
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block
UPC	822350531153

**Physical**

Circuits (Loaded)	6
Entry Angle	Vertical
Lock to Mating Part	Yes
Net Weight	10.120/g
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm²	0.13 - 3.31

**Electrical**

Current - Maximum per Contact	18A
Voltage - Maximum	300V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-39500-001, RPS-39500-001
Sales Drawing	SD-39530-001



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[39530Series](#)

**Mates With**

[39531 Vertical PCB Header](#), [39532  
Horizontal PCB Header](#), [39538 Dual Level  
PCB Header](#), [Open Ends](#), [Most 5.08mm  
Pitch Industry Standard PCB Headers](#)