

Screwdriver - SZS 0,4X2,5 VDE - 1205037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

The illustration shows version SZS
0,6 x 3,5

Why buy this product

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head
- Individually tested safety screwdrivers according to DIN EN 60900 (VDE 0682-201)
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 019075
Weight per Piece (excluding packing)	31.4 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	161 mm
Width (a)	26 mm
Blade thickness	0.4 mm
Blade width	2.5 mm
Blade height	80 mm

General

Type	Bladed
Material	Alloyed tool steel
Test standard	DIN/ISO 2380-1 IEC 60900:2004

Screwdriver - SZS 0,4X2,5 VDE - 1205037

Classifications

eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401
eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040409

ETIM

ETIM 2.0	EC000158
ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC000158

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals

Approvals

VDE Zeichengenehmigung / GOST / GOST

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung

Screwdriver - SZS 0,4X2,5 VDE - 1205037

Approvals

GOST

GOST

Drawings

Pictogram



Dimensioned drawing

