

## Crimping pliers - CRIMPFOX 10S - 1212045


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>, unlockable pressure lock, lateral entry

### Why buy this product

- ✓ These compact crimping pliers have been designed to reduce effort when working
- ✓ The way in which the handles and the die are arranged means that the ferrules can be fitted however the tool is held



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 455732
Weight per Piece (excluding packing)	439.7 g
Custom tariff number	82032000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	175 mm
------------	--------

#### General

Compression	Square crimp
Type of contact	Insulated and uninsulated ferrules

### Classifications

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301

# Crimping pliers - CRIMPFOX 10S - 1212045

## Classifications

### eCl@ss

eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

GOST 
--

## Accessories

Accessories

Mounting material

## Crimping pliers - CRIMPFOX 10S - 1212045

### Accessories

Replacement spring - CRIMPFOX/SPR-2 - 1212047



Spare recuperating spring