



Illustrations



Dimensions



PCB layout



see enlarged drawings at the end of document


Product Information

- PC board jack RJ45, shielded
- multi port 1x4, side entry, with 8 contacts
- solderable, color metal
- L x W x H: 15.75 x 63.76 x 13.3 mm
- LED, yellow/green


Technical Data

Soldering method	THT
Rated voltage max.	150 V
Rated Current	1 A
Contact resistance	50 mOhms
Insulation resistance	500 MOhms
Dielectrical Withstanding Voltage between contacts	1000 Vrms
between contacts and shield	1500 Vrms
Contact material	CuSn
Contact surface	selective 5 μ"gold
Shield material	copper alloy
Shield surface	Ni
Mating force max.	22.55 N
Durability plug cycles	<= 750
Insulation material	PBT, UL94V-0
Insulation color	black
Operating Temperature	-40 °C to 85 °C
Type of protection	IP20
LED 1 / LED 2	yellow / green

Dimensions



PCB layout



© 2013 METZ CONNECT - Technische Änderungen vorbehalten! Subjects to modifications!