

## 6430

Festoon lamps for trucks



### Areas of application

- Number plate and side position lights
- Interior lighting and reading lights

### Product benefits

- OEM Quality
- Wide product range
- Reliable quality

### Product features

- Original spare parts

---

## Technical data

---

### Electrical data


Power input	3 W
Nominal wattage	3 W
Nominal voltage	24 V
Power input tolerance	±10 %
Test voltage	28.0 V

### Light technical data

Luminous flux	22 lm
Luminous flux tolerance	±20 %

### Dimensions & weight

---



Product line drawing

---

Length	28.0 mm
Diameter	8.0 mm
Product weight	1.79 g

### Lifespan

Lifespan B3	400 h
Lifespan Tc	800 h

### Additional product data

Base (standard designation)	SV7
-----------------------------	-----

### Certificates & standards

---

## Product datasheet

<b>ECE category</b>	-
---------------------	---

### Country specific categorizations

<b>Order reference</b>	6430
------------------------	------

---

### Country specific information

<b>Product code</b>	<b>METEL code</b>	<b>SEG-No.</b>	<b>STK-Number</b>	<b>UK Org</b>
4008321094414	OSRA6430	-	-	-

## Product datasheet

---

### Logistical Data

---

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321094414	6430	Unpacked 1	7 mm x 7 mm x 28 mm	0.00 dm <sup>3</sup>	4.00 g
4008321094520	6430	Folding carton box 10	145 mm x 53 mm x 37 mm	0.28 dm <sup>3</sup>	37.00 g
4008321094537	6430	Shipping carton box 50	144 mm x 64 mm x 205 mm	1.89 dm <sup>3</sup>	209.50 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.