

64113

MINIWATT | Signal lamps for cars and motorcycles



Areas of application

- Interior lighting and reading lights

Product benefits

- OEM Quality
- Wide product range
- Reliable quality

Product features

- Hard-glass technology
- High luminous flux
- Luminous flux constant throughout the life of the lamp
- High color temperature (white light)
- Original spare parts

Technical data



Electrical data

Power input	10 W
Nominal wattage	10 W
Nominal voltage	12 V
Power input tolerance	±7.5 %
Test voltage	13.5 V

Light technical data

Luminous flux	200 lm
Luminous flux tolerance	±15 %

Dimensions & weight



Product line drawing

Base

Length	33.0 mm
Diameter	9.0 mm
Product weight	2.28 g

Lifespan

Lifespan B3	150 h
Lifespan Tc	400 h

Additional product data

Base (standard designation)	BA9s
-----------------------------	------

Certificates & standards

Product datasheet

ECE category	-
---------------------	---

Country specific categorizations

Order reference	64113
------------------------	-------

Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
4008321095046	OSRA64113	-	4739540	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321095046	64113	Unpacked 1	10 mm x 10 mm x 27 mm	0.00 dm ³	3.00 g
4008321095053	64113	Folding carton box 10	142 mm x 53 mm x 36 mm	0.27 dm ³	35.80 g
4008321095060	64113	Shipping carton box 50	144 mm x 64 mm x 205 mm	1.89 dm ³	229.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.