

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [43938-2101](#)
Status: **Active**
Overview: Mini-Fit Sr.™ Power Connectors
Description: 10.00mm Pitch Mini-Fit Sr.™ Plug Housing, Dual Row, Panel Mount, 6 Circuits

Documents:

[3D Model](#) [Test Summary TS-42815-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-42815-001 \(PDF\)](#)

Agency Certification

CSA LR19980
TUV R72081037
UL E29179

General

Product Family Crimp Housings
Series [43938](#)
Application Power, Wire-to-Wire
Overview [Mini-Fit Sr.™ Power Connectors](#)
Product Name Mini-Fit Sr.™
UPC 800753009790

Physical

Circuits (maximum) 6
Color - Resin Black
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Material - Resin Polyester
Net Weight 12.261/g
Number of Rows 2
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 10.00mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 50A

Material Info

Reference - Drawing Numbers

Product Specification PS-42815-001, RPS-42815-001, RPS-42815-012,
RPS-42815-013, RPS-42815-015
Sales Drawing SD-43938-002
Test Summary TS-42815-001




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[43938Series](#)

Mates With

[43914](#)

Use With

[42817](#) Male Terminal and [43980](#) TPA Clip