

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19001-0010](#)
Status: **Active**
Description: Avikrimp™ Quick Disconnect, Male, for 10-12 (5.00-3.30mm²), Box, Tab 6.35 x 0.81mm

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-014 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)

Agency Certification

CSA LR18689
TUV R9071070
UL E79133

General

Product Family Quick Disconnects
Series [19001](#)
Crimp Quality Equipment Yes
Insulated Fully
Product Name Avikrimp™
Type Quick Disconnect
UPC 800753026650

Physical

Barrel Type Closed
Color - Resin Yellow
Flammability 94V-2
Gender Male
Glow-Wire Compliant No
Insulation Nylon (PA)
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Zinc Chromate
Material - Plating Termination Zinc Chromate
Net Weight 2.359/g
Orientation Straight
Packaging Type Bag
Polarized to Mating Part No
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating -65°C to +105°C
Wire Insulation Diameter 5.84mm max.
Wire Size AWG 10, 12
Wire Size mm² 3.30 - 5.00

Electrical

Voltage - Maximum 300V

Material Info

Old Part Number C-5264

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013, PS-19902-014
Sales Drawing SD-19001-002




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19001Series](#)

Use With

[19002-0044](#) , [19002-0045](#) , [19002-0046](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640014600
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640054600

This document was generated on 07/04/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION