



SYLVANIA



OSRAM



Sylvania Automotive Lamp Catalog

Housing and Lens Assemblies

T-2 Indicator Slide Base Lamps

T-2 Pilot Slide Base Lamps

T-2 1/2 Miniature Bayonet Base Lamps

T-2 Indicator Cartridge Lamps

T-2 Pilot Cartridge Lamps



T-3 1/4 Miniature Bayonet Base Lamps

Universal Lamp Housings

Line No.	Color	Flat Top Translucent	Jeweled	Dome Transparent	Dome Translucent*	Dome Fluted
1	Red	30200	30100	30110	30130	30120
2	Green	30212	30102	30112	30132	30122
3	Blue	-	-	30113	-	30124
4	Amber	-	30106	30111	-	30126
5	Yellow	30214	-	-	30131	-
6	Clear	-	-	30116	-	30125
7	White	-	-	-	30133	-

* 180°C maximum temperature

T-2 Pilot Housing

	File No. E146431 (M)
	File No. LR77103

Flat Top Translucent Jeweled Dome Transparent Dome Fluted

Choose your lens and color...



Add a T-2 Pilot lamp...

Lamp



Neoprene Washers

And insert into socket



#30099
Socket

Dimensions

Lenses: Diameter 0.63" ; Height: 0.38"
Socket: Front of panel to end of terminals: 0.91"
Mounting Hole: 0.719" diameter

Tab Size

.205" Blade Width
.016" Thick
.070 in. hole Diameter