



Max. On State Voltage Drop [rms]	0.5 VAC
----------------------------------	---------

## INPUT CHARACTERISTICS

Input Voltage Range	4 to 32 VDC
Maximum Turn-On Voltage	4 VDC
Minimum Turn-Off Voltage	1 VDC
Must Release Voltage	1 VDC
Typical Input Current	9 to 11 mA

## MISCELLANEOUS CHARACTERISTICS

Operating Time (Response Time) - Off	1 ms
Ambient Air Temperature around the Device - Storage	-40 to +125 °C
Ambient Air Temperature around the Device - Operation	-40 to +80 °C
Terminal Torque (Maximum)	6 in lb
Recommended Terminal Screw Torque Range	Input: 5 to 6 in lb Output: 5 to 60 in lb Input: 0.6 to 0.7 N·m Output: 0.6 to 0.7 N·m
Degree of Protection	IP 20
LED Input	Green