


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0065](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel

Documents:

Drawing (PDF)	Product Specification PS-5556-002 (PDF)
Product Specification PS-54111-002 (PDF)	Packaging Specification PK-5556-001 (PDF)
Product Specification PS-54452-007 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-5556-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800753584709

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	128.200/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5556PBT2
-----------------	----------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-54111-002, PS-54452-007, PS-5556-001, PS-5556-002, RPS-54111-004
Sales Drawing	SD-5556****
Test Summary	TS-5556-002

EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen	China RoHS 
---	--

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5556Series](#)

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Crimp Terminals	0638191000
FineAdjust™ Applicator for	0639023800

Insulation OD 0.95-1.08mm - 22-28 AWG T2 Terminator™	<u>0639123800</u>
for insulation OD 0.95-1.08mm - 22-28 AWG FineAdjust™	<u>0639002700</u>
Applicator for Insulation OD 1.30-1.50mm - 22-28 AWG T2 Terminator™	<u>0639102700</u>
for insulation OD 1.30-1.50mm - 22-28 AWG FineAdjust™	<u>0639020200</u>
Applicator for Insulation OD 1.10-1.30mm - 22-28 AWG T2 Terminator™	<u>0639120200</u>
for insulation OD 1.10-1.30mm - 22-28 AWG Extraction Tool	<u>0011030044</u>
Japan	
Description	Product #
Applicator for M21 1A	<u>0570383000</u>
Bench Press, 22-28 AWG Wire	

This document was generated on 06/27/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION