

TY25M

Ty-Rap®

Bulk - Standard Nylon 6/6 cable ties. Body width of 0.185 in. and a length of 7.31 in. Maximum wire bundle diameter 1.75 in.

General

Type:	Ty-Rap Cable Ties
MIL-SPEC:	MS3367-1
Color:	Natural
T&B UPC:	78621082457
T&B Status:	M
Material:	Nylon 6/6

Dimension Information

Body Width (in.):	0.190
Body Width (mm):	4.83
Length (in.):	7.31
Length (mm):	185.67
Tensile Strength (lb):	50
Max. Wire Bundle Dia. (in.):	1.75
Temperature Range:	-40°F to 185°F (-40°C to 85°C)