

SMNY-220-9-D



Catamount™

4-Way screw mounts for cable ties to 50# tensile strength. Mount with #6 or #8 screws.

General

Type:	Cable Tie Mounting Bases
Color:	Natural
T&B UPC:	72849412252
T&B Status:	M
Material:	Nylon 6/6

Dimension Information

Height (in.):	0.23
Height (mm):	5.84
Length (in.):	0.95
Length (mm):	25.13
Width (in.):	0.5
Width (mm):	12.7
Slot Width (in.):	0.22
Slot Width (mm):	5.59
Temperature Range:	-40°F to 185°F (-40°C to 85°C)