

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [10-01-3036](#)
Status: **Active**
Overview: SPOX™ Wire-to-Board Connectors
Description: 5.08mm Pitch SPOX™ Crimp Terminal Housing, 3 Circuits

Documents:

[3D Model](#) [Product Specification PS-5197-005 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5197-001 \(PDF\)](#)

Agency Certification

CSA LR19980
TUV R72090224
UL E29179

General

Product Family Crimp Housings
Series [5197](#)
Application Signal, Wire-to-Board
Overview [SPOX™ Wire-to-Board Connectors](#)
Product Name SPOX™
UPC 800754313124

Physical


Circuits (maximum) 3
Color - Resin Natural
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 1151.200/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 5.08mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Material Info

Old Part Number 5197-03

Reference - Drawing Numbers

Product Specification PS-5197-001, PS-5197-005, RPS-5281-001
Sales Drawing SD-5197-N



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5197Series

Mates With

5279 , 5280 , 5281 , 5282

Use With

5194 , 5225