

Master Heat Guns & Kits



Master Heat Gun®



Description

Professional quality, heavy-duty industrial, multiple use heat guns & kits

- High temperature and power ratings: 1000°F/540°C at up to 1740 watts, accommodates many industrial and commercial heating applications
- High air flow rating: 23 CFM at 3000 FPM gets the job done fast
- Powerful high speed universal motor
- Sturdy die cast housing
- Adjustable non-slip stand
- Kits include Heat Gun, A-160-HG Shrink Attachment, 51543 Spreader Attachment & 51544 Reducer Attachment & 51013 Storage Case
- Use to bend plastics, cure adhesives, dry parts, heat parts, shrink tubing and packaging, strip paint and more
- Optional Momentary Contact Switch turns heat gun off when operator is not pressing it. To order, add "MC" suffix to the model number. Example: HG-501A-MC

Available Models

120V MODELS

MODEL NO.	DESCRIPTION						REPLACEMENT ELEMENT
HG-201A	200-300°F	93-150°C	120V	60Hz	5A	600W	HAS-042K
HG-301A	300-500°F	150-260°C	120V	60Hz	12A	1440W	HAS-041K
HG-501A	500-750°F	260-400°C	120V	60Hz	14A	1680W	HAS-011K
HG-751B	750-1000°F	400-540°C	120V	60Hz	14.5A	1740W	HAS-043K

120V MODEL KITS

MODEL NO.	DESCRIPTION						REPLACEMENT ELEMENT
HG-201AK	200-300°F	93-150°C	120V	60Hz	5A	600W	HAS-042K
HG-301AK	300-500°F	150-260°C	120V	60Hz	12A	1440W	HAS-041K
HG-501AK	500-750°F	260-400°C	120V	60Hz	14A	1680W	HAS-011K
HG-751BK	750-1000°F	400-540°C	120V	60Hz	14.5A	1740W	HAS-043K

220V MODELS

MODEL NO.	DESCRIPTION						REPLACEMENT ELEMENT
HG-202A	200-300°F	93-150°C	220V	50Hz	3A	600W	HAS-012K
HG-302A	300-500°F	150-260°C	220V	50Hz	6A	1440W	HAS-013K
HG-502A	500-750°F	260-400°C	220V	50Hz	7A	1680W	HAS-014K
HG-752A	750-1000°F	400-540°C	220V	50Hz	9A	1740W	HAS-016K

Specifications

Avg. Air Volume: 23 CFM

Avg. Air Velocity: 3000 FPM

Motor: Universal

Nozzle Opening: 1.2" Diameter I.D.

Dimensions: 9" L x 5.2" W x 10.1" H

Cordset: 6 ft., 3-wire grounded

Net Weight - Single Unit 3.7 lbs., Kit: 8 lbs.

Shipping Weight - Single Unit: 5 lbs., Kit: 10 lbs.