

Specification Sheet

KAZAM

Brand	KAZAM
Tier	Entry
Model	KAZAM Trooper X3.5
Available Colours	Dark Blue/White/Black



It's not the size, it's what you do with it

Small and mighty, the KAZAM Trooper X3.5 is compact in size but packs a performance punch, thanks to its Dual Core 1GHz processor and Android version 4.2 - Jelly Bean.

Main Specification

Chipset	MT6572M	ROM	4GB
Cores	Dual	RAM	512MB
GPU	Mali-400 MP	Frequency/Clock Speed	1 GHz
SD Card Slot	YES	SD Expandable To	32GB
SIM Card Slots	2	SIM Slot Sizes	2 x Normal
Size (mm)	113 x 63 x 12.5	Weight (with battery)	118g
GSM Bands (MHz)	850/900/1800/1900	3G Bands (MHz)	900/2100
LTE Bands (MHz)	N/A	Android Version	4.2.2

Screen/Camera/Audio

Display	Size	3.5"
	Type	TFT
	Resolution	320 x 480
	Touch Screen	YES
Rear Camera	HW Resolution	3Mp
	Type	Fixed-focus
	Flash	YES
	Video	720p/30fps
Front camera	Resolution	0.3Mp
	Type	Fixed-focus
Audio	Audio Jack	3.5mm
	Speakers	Single

Connectivity/Sensors

Bluetooth	YES / 3.0
Sensors	G-Sensor/Proximity Sensor/Ambient Light Sensor
WIFI	Wi-Fi (Type: 2.4Ghz / 802.11 b/g/n), Wi-Fi hotspot
GPS	YES
FM-radio	YES (via earphones)
NFC	NO

Charging/Battery/Certifications

I / O	Type	USB: Mass Storage / Media (MTP) / Camera (PTP) / Debugging
Battery	Removable	YES
	Type	Li-Polymer
	Size	1300mAh
	Weight	29g
	Standby time	240 hours
	Talk Time	5 hours
Charger		USB
SAR Value: Body/Head		0.629W/kg@10g (CE) / 0.835W/kg@10g (CE)
Certification		CE/RoHS/WEEE/GMS/CTS